



CONNECTOR POSITION
RECOMMEND PCB LAYOUT

■ SPECIFICATIONS

- Voltage rating: 250V AC, DC
- Current rating: 1A, AC, DC
- Withstanding voltage: 250V AC/minute
- Insulation resistance: 100MΩmin
- Temperature range: -40°C - +105 °C
- Contact resistance: 20mΩ max



■ WAFER

- Part No. :CS-1147V-14
- Poles:2-16
- Material:LCP, UL94V-0
- Contact:Brass (C2680), Tin plated
- Q' TY:1,000 pcs/bag




	+0.15
	-0.15

0.30



2~3P 一个窗口



4~15P 两个窗口

Poles	PART NO	DIMENSION (mm)	
		A	B
2	CS-1147V-02	1.25	4.25
3	CS-1147V-03	2.50	5.50
4	CS-1147V-04	3.75	6.75
5	CS-1147V-05	5.00	8.00
6	CS-1147V-06	6.25	9.25
7	CS-1147V-07	7.50	10.50
8	CS-1147V-08	8.75	11.75
9	CS-1147V-09	10.00	13.00
10	CS-1147V-10	11.25	14.25
11	CS-1147V-11	12.50	15.50
12	CS-1147V-12	13.75	16.75
13	CS-1147V-13	15.00	18.00
14	CS-1147V-14	16.25	19.25
15	CS-1147V-15	17.50	20.50

RoHS 2.0

本圖紙知識產權及版權由永丰盈有限公司所有,未經書面許可不准擅自傳閱、复制和修改.本公司保留法律追究的权利.

类别	WAFER	品名	CS-1147V-14	X.	±0.50	材料		单位	mm	SHEET 1 OF 1	
版本	B/0	设计	李文畅	X.X	±0.30	颜色		比例	1:1		修改内容 修改日期
制定部门	工程课	绘制	李文畅	X.XX	±0.20	画法		数量			加储存方式 2017-08-10
工程图号	CST-001147V	审核	姚培柱	X.XXX	±0.10	CST 深圳市永丰盈电子有限公司 ShenZhenYongFengYing ELECTRONICS CO.,LTD.					窗口视图 2022-10-24
制定日期	2022-10-24	核准	周中湖	X.XXXX	±0.05						

CST 深圳市永丰盈电子有限公司
ShenZhenYongFengYing ELECTRONICS CO.,LTD.