





SPECIFICATIONS

- Rated Voltage: 250V AC, DC
- Current rating: 12A, AC, DC
- Withstanding Voltage: 1,500V AC/minute
- Insulation resistance: 1,000MΩ Min
- Temperature range: -40°C to +105°
- Contact resistance: 20mΩ max

TERMINAL

- Part No: CS-1149-T 18 HJ G
- T: 端子
- G: 镀半金1u"
- 18: 低脚 (包AWG18#)
- HJ: 合金铜

- WIRE RANGE: AWG#18
- Material: Alloy Copper (550)
- Thickness: 0.20mm
- Finish: Tin Plated/Gold Plated
- Q' TY: 10,000 pcs/reel



RoHS 2.0

\* 本圖紙知識產權及版權由永丰盈电子有限公司所有, 未經許可不准擅自复制和修改. 本公司保留法律追究的权利.

VERSION	DATE	ENGINEER	CHECK BY	DESIGNER	APPROVE	PROJECTION	MATERIAL	MOLD NO	UNIT	SCALE	SHEET 1 OF 1		
A/0	2020. 10. 30	WENCHANG LI	ZHOU ZHONGHU	WENCHANG LI	HUANG HAI GENG	第一角	CS-1149-T18HJG		mm	1:1	△1	REVISE	REVISE DATE
FRAME		DEPARTMENT									△2		
							永丰盈电子有限公司				△3		
							YONG FENG YING ELECTRONIC CO., LTD.						