





### SPECIFICATIONS

- Rated Voltage: 250V AC, DC
- Current rating: 12A, AC, DC
- Withstanding Voltage: 1,500V AC/minute
- Insulation resistance: 1,000MΩ Min
- Temperature range: -40°C to +105°
- Contact resistance: 20mΩ max

### TERMINAL

- Part No: CS-1149-T 18 HJ T
- T: 端子
- 18: 低脚 (包AWG18#)
- HJ: 合金铜
- T: 镀亮锡
- G: 镀半金1u"

- WIRE RANGE: AWG#18
- Material: Alloy Copper (550)
- Thickness: 0.20mm
- Finish: Tin Plated/Gold Plated
- Q' TY: 10,000 pcs/reel



RoHS 2.0

\* 本圖紙知識產權及版權由永丰盈电子有限公司所有, 未經許可不准擅自复制和修改. 本公司保留法律追究的权利.

VERSION	DATE	ENGINEER DEPARTMENT	CHECK BY	DESIGNER	DATE	±0.50	±0.30	±0.20	±0.10	±0.05	MATERIAL	PROJECTION	MOLD NO	UNIT	SCALE	SHEET 1 OF 1
FRAME	DRAWING NO.	DATE	APPROVE	CHECK BY	DESIGNER	±0.50	±0.30	±0.20	±0.10	±0.05	永丰盈电子有限公司	YONG FENG YING ELECTRONIC CO., LTD.		mm	1:1	REVISION
VERSION	DATE	ENGINEER DEPARTMENT	CHECK BY	DESIGNER	DATE	±0.50	±0.30	±0.20	±0.10	±0.05						REVISION
FRAME	DRAWING NO.	DATE	APPROVE	CHECK BY	DESIGNER	±0.50	±0.30	±0.20	±0.10	±0.05						REVISION