


SPECIFICATIONS

- Rated Voltage: 250V AC, DC
- Current rating: 7-9A, AC, DC
- Withstanding Voltage: 1,500V AC/minute
- Insulation resistance: 1,000 Ω Min
- Temperature range: -40°C to +105°
- Contact resistance: 20m Ω max

TERMINAL

- Part No: CS-1149-T 18 XX DN G
- T: 端子
- T: 镀锡
- G: 镀半金1u"
- S: 先冲后镀 亮锡
- 18: 低脚 (包AWG18#)
- DN: 紧锁, 大接触点
- XX: 新型四面弹片结构

- WIRE RANGE: AWG#18
- Material: Phosphor Bronze (C5191)
- Thickness: 0.20mm
- Finish: Tin Plated/Gold Plated
- Q' TY: 10,000 pcs/reel



RoHS 2.0

* 本圖紙知識產權及版權由永丰盈电子有限公司所有, 未經許可不准擅自复制和修改. 本公司保留法律追究的权利.

SORT	TERMINAL	PART NO.	CS-1149-T18XXDNG	X.	±0.50	MATERIAL	C5191-H	MOLD NO.		SHEET 1 OF 1		
VERSION	B/0	DESIGNER	WENCHANG LI	X.X	±0.30	RIGIDITY	190° -210°	UNIT	mm	△1	REVISE	REVISE DATE
FRAME	ENGINEER DEPARMENT	DRAW BY	WENCHANG LI	X.XX	±0.20	PROJECTION		SCALE	1:1	△1	紧锁, 大接触面	2022-10-24
DRAWING NO.	CS-1149-T18XXT	CHECK BY	ZHOU ZHONGHU	X.XXX	±0.10	永丰盈电子有限公司 YONG FENG YING ELECTRONIC CO., LTD.			△2			
DATE	2022. 10. 24	APPROVE	HUANG HAI GENG	X.XXXX	±0.05				△3			