





SPECIFICATIONS

- Rated Voltage: 250V AC, DC
- Current rating: 7-9A, AC, DC
- Withstanding Voltage: 1,500V AC/minute
- Insulation resistance: 1,000MΩ Min
- Temperature range: -40°C to +105°
- Contact resistance: 20mΩ max

TERMINAL

- Part No: CS-1149-T 218 XX DN G
- T: 端子
 G: 镀半金1u"
 G3: 镀半金3u"
 S: 先冲后镀 亮锡
 DN: 紧锁, 大接触点
- 218: 高脚 (包双线2*AWG18#)
 XX: 新型四面弹片结构

- WIRE RANGE: AWG#18*2
- Material: Phosphor Bronze (C5191)
- Thickness: 0.20mm
- Finish: Tin Plated/Gold Plated
- Q' TY: 5,000 pcs/reel



RoHS 2.0

* 本圖紙知識產權及版權由永丰盈电子有限公司所有, 未經許可不准擅自复制和修改. 本公司保留法律追究的权利.

SORT	TERMINAL	PART NO.	CS-1149-T218XXDN	X.	±0.50	MATERIAL	C5191-H	MOLD NO		SHEET 1 OF 1		
VERSION	B/0	DESIGNER	WENCHANG LI	X. X	±0.30	RIGIDITY	190° -210°	UNIT	mm	⚠	REVISE	REVISE DATE
FRAME	ENGINEER DEPARTMENT	DRAW BY	WENCHANG LI	X. XX	±0.20	PROJECTION		SCALE	1:1	⚠	紧锁, 大接触面	2022-10-24
DRAWING NO.	CS-1149-T18XXX	CHECK BY	ZHOU ZHONGHU	X. XXX	±0.10	永丰盈电子有限公司 YONG FENG YING ELECTRONIC CO., LTD.				⚠		
DATE	2022. 10. 24	APPROVE	HUANG HAI GENG	X. XXXX	±0.05					⚠		