


SPECIFICATIONS

- Rated Voltage: 250V AC, DC
- Current rating: 7-9A, AC, DC
- Withstanding Voltage: 1,500V AC/minute
- Insulation resistance: 1,000MΩ Min
- Temperature range: -40°C to +105°
- Contact resistance: 20mΩ max

TERMINAL

- Part No: CS-1149-T 218 XX T
- T: 端子 (Terminal)
- G: 镀半金1u" (Half gold plating 1u")
- S: 先冲后镀 亮锡 (Plating after punching, bright tin)
- XX: 新型四面弹片结构 (New four-sided spring structure)
- 218: 高脚 (包双线2*AWG18#) (High foot (2*AWG18# double wire))

- Wire Range: AWG#18*2
- Material: Phosphor Bronze (C5191)
- Thickness: 0.20mm
- Finish: Tin Plated/GOLD PLATED
- Q'TY: 10,000 pcs/reel



RoHS 2.0

* 本圖紙知識產權及版權由永丰盈电子有限公司所有, 未經許可不准擅自复制和修改. 本公司保留法律追究的权利.

SORT	TERMINAL	PART NO.	CS-1149-T218XXT	X.	±0.50	MATERIAL	C5191-H	MOLD NO		SHEET 1 OF 1		
VERSION	D/O	DESIGNER	WENCHANG LI	X.X	±0.30	RIGIDITY	190° -210°	UNIT	mm	▲1	REVISE	REVISE DATE
FRAME	ENGINEER DEPARTMENT	DRAW BY	WENCHANG LI	X.XX	±0.20	PROJECTION		SCALE	1:1	▲1		
DRAWING NO.	CS-1149-T16XXG	CHECK BY	ZHOU ZHONGHU	X.XXX	±0.02	永丰盈电子有限公司 YONG FENG YING ELECTRONIC CO., LTD.				▲2		
DATE	2023.08.15	APPROVE	HUANG HAI GENG	X.XXXX	±0.01					▲3		