

5148417-5 ✓ ACTIVE

EUROCARD | EUROCARD TYPE M


TE Internal #: 5148417-5

Eurocard Connectors, Receptacle, Board-to-Board, 78 Position, .1 in [2.54 mm] Centerline, Printed Circuit Board, 3 Row, Vertical, EUROCARD TYPE M

[View on TE.com >](#)



Connectors > PCB Connectors > Backplane Connectors > Eurocard Connectors



Connector & Housing Type: **Receptacle**

Connector System: **Board-to-Board**

Termination Post & Tail Length: **4.83 mm [.19 in]**

Number of Positions: **78**

Centerline (Pitch): **2.54 mm [.1 in]**

Features

Product Type Features

Connector & Housing Type	Receptacle
Connector System	Board-to-Board
Connector & Contact Terminates To	Printed Circuit Board
DIN Size	Half
DIN Level	II

Configuration Features

Number of Power or Coaxial Positions	2
Number of Positions	78
Number of Rows	3
PCB Mount Orientation	Vertical
Number of Columns	26
Number of Signal Positions	78
Rows Loaded	A, B, C

Body Features



Primary Product Color	Gray
-----------------------	------

Contact Features

Contact Type	Socket
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	3 A

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Press-Fit
Termination Post & Tail Length	4.83 mm[.19 in]

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Housing Material	Polymer - GF
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

PCB Thickness (Recommended)	1.57 mm[.062 in]
Row-to-Row Spacing	2.54 mm[.1 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Box
------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235)



Candidate List Declared Against: JUNE 2023 (235)
Does not contain REACH SVHC

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 148411-5
EURO TYPE M PIN ASSY 78+2



TE Part # 148375-1
EURO, TYPE M CONTACT, FEMALE



TE Part # 5148411-5
ASSY,PIN,R.A.,TYPE M,EUROCARD,L-FREE,78+



TE Part # 1-1393645-7
V42254B1200M780=PC612 MESSERLE

Also in the Series | EUROCARD TYPE M



Eurocard Connectors(19)

Customers Also Bought



TE Part #5788793-1
09 HTMSFL PLUG RA 318 (SL,BL)



TE Part #1060985-1
5862 5002 10,OSX JACK RECPT



TE Part #4-641215-0
10P MTA100 HDR ASSY FL/ST 30AU




TE Part #3-1879336-3
CPF 0603 499R 1% 50PPM 1K RL




TE Part #4-794629-2
12P MICRO MNL ASSY,R/A,SMT,LF



TE Part #215605-1
96P.IEC-C MALE CONN



TE Part #63067-1
250 FASTON TAB TPBR



TE Part #1375795-2
PC104 ASY STKTHRU UNKEYED



TE Part #2-530745-2
MINI BX RECPT ASSY 128P SEALED

Documents

Product Drawings

[ASSY,RECPT,TYPE M,EUROCARD,L-F](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_5148417-5_O.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5148417-5_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5148417-5_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Application Specification

English