

(1.27 mm) .050"

YFS SERIES

LOW PROFILE OPEN-PIN-FIELD SOCKET

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?YFS

Insulator Material:
Black Liquid Crystal Polymer Contact Material:
Phosphor Bronze
Plating:
Au over 50 µ" (1.27 µm) Ni
Operating Temp Range:
-55 °C to +125 °C
Working Voltage:
275 VAC when mated
with YFT
Mated Cycles:

RoHS Compliant: No Lead-Free Solderable: No


RECOGNITIONS


For complete scope of recognitions see www.samtec.com/quality



ALSO AVAILABLE (MOQ REQUIRED)

- 30, 40 & 50 positions in 5 & 8 rows
- 3 & 6 rows





(1.27).050

(3.40)

Note:

Some sizes, styles and options are non-standard, non-returnable.

(0.76) .030 – DIA