



- SPECIFICATIONS**
- Current Rating: 2A AC, DC
 - Voltage Rating: 250V AC, DC
 - Temperature Range: -25°C~ +85°C
 - Contact Resistance: 20mΩ Max
 - Insulation Resistance: 1000mΩ Min
 - Withstanding Voltage: 1000V AC/minute
 - Material: Wafer Nylon66 UL94-VO (2)
Pin Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	XD-HY-2A-L	2.00	6.00
3	XD-HY-3A-L	4.00	8.00
4	XD-HY-4A-L	6.00	10.00
5	XD-HY-5A-L	8.00	12.00
6	XD-HY-6A-L	10.00	14.00
7	XD-HY-7A-L	12.00	16.00
8	XD-HY-8A-L	14.00	18.00
9	XD-HY-9A-L	16.00	20.00
10	XD-HY-10A-L	18.00	22.00
11	XD-HY-11A-L	20.00	24.00
12	XD-HY-12A-L	22.00	26.00
13	XD-HY-13A-L	24.00	28.00
14	XD-HY-14A-L	26.00	30.00
15	XD-HY-15A-L	28.00	32.00
16	XD-HY-16A-L	30.00	34.00

Ordering Information

XD - HY - N *** - * - **

Pin	Type	Colour	Contact Plating
	Y=直插 A=直插 AW=弯脚 AWD=定位弯脚	默认=本色 R=红色 G=绿色 B=蓝色 F=黄色 V=紫色	默认=Sn G1.0μ"/Gold G2.0μ"/Gold G3.0μ"/Gold G4.0μ"/Gold G5.0μ"/Gold

			GENERAL TOLERANCE	制图 DRAWING	10	深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd			
			DIM TOL	审核 CHECK					
			X.X ±0.30	批准 APPROVAL		产品名称 TITLE	HY (2.00) 单排带扣 直针 蓝色	版本 REV.	A
			X.XX ±0.20	比例 SCALE		产品料号 PART NO.	XD-HY-NA-L	单位 UNITS	mm
			X.XXX ±0.10	投影 Projection		材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°						