



修订 REV	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
AO		NEW DWG		2023-09-25





- ◆SPECIFICATIONS
- Current rating: 2.0A AC, DC
 - Voltage rating: 250V AC,DC
 - Temperature range: -25°C ~ +85°C
 - Insulation resistance: 500MΩ Min.
 - Withstanding voltage: 500V AC/minute.
 - Contact resistance: 20m Ω Max.


Material:
 Insulator: Nylon 46 UL 94V-0
 Suitable: HDGC1508-T series Terminal,
 HDGC1508HM-2xXP series Dual Row Housing
 HDGC1508WV / WVA-2xXP、WR/WRA-2xXP
 HDGC1508WV / WVA-S-2xXP、WR/WRA-S-2xXP
 series Dual Row Wafer.

	2x20P	32.25	31.52	30.00	28.50	10.50	30.52
2x19P	30.75	30.02	28.50	27.00	10.50	29.02	
2x18P	29.25	28.52	27.00	25.50	10.50	27.52	
2x17P	27.75	27.02	25.50	24.00	10.50	26.02	
2x16P	26.25	25.52	24.00	22.50	10.50	24.52	
2x15P	24.75	24.02	22.50	21.00	10.50	23.02	
2x14P	23.25	22.52	21.00	19.50	10.50	21.52	
2x13P	21.75	21.02	19.50	18.00	10.50	20.02	
2x12P	20.25	19.52	18.00	16.50	10.50	18.52	
2x11P	18.75	18.02	16.50	15.00	10.50	17.02	
2x10P	17.25	16.52	15.00	13.50	10.50	15.52	
2x9P	15.75	15.02	13.50	12.00	10.50	14.02	
2x8P	14.25	13.52	12.00	10.50	4.50	12.52	
2x7P	12.75	12.02	10.50	9.00	4.50	11.02	
2x6P	11.25	10.52	9.00	7.50	4.50	9.52	
2x5P	9.75	9.02	7.50	6.00	4.50	8.02	
2x4P	8.25	7.52	6.00	4.50	4.50	6.52	
2x3P	6.75	6.02	4.50	3.00	3.00	5.02	
2x2P	5.25	4.52	3.00	1.50	2.50	3.52	
Circuits Part NO.	A	B	C	D	E	F	
	Dimensions						




A - A





深圳市华德共创科技有限公司
 Shenzhen Huade co-create Technology Co.,LTD
 电话: 0755-27129737 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		 	TITLE: 产品名称: HDGC1.5带扣公壳				
X.X	±0.15	X.X*	±3'	APPD: 核准: 谢亮		PART NO: 产品编号: HDGC1500HA-2xXP	
X.XX	±0.05	X.XX*	±2'	CHECK: 校对: 王建业	DATE	SCALE	UNIT
X.XXX	±0.03	X.XXX*	±1'	DRAW: 绘图: 黄艳兰	2023-09-25	1:1	mm
					CODE NUMBER	A001	