



1504 尼龍絕緣公母插 (母)
NYLON INSULATED FEMALE LUG

型號 ITEM NO.	T (mm)	單價
PN1.25-7A	0.8	2.4
PN2-7A	0.8	2.4
PN5.5-7A	0.8	3.0



1504 尼龍絕緣公母插 (公)
NYLON INSULATED MALE LUG

型號 ITEM NO.	T (mm)	單價
PN1.25-7B	0.8	2.6
PN2-7B	0.8	2.6
PN5.5-7B	0.8	3.2



1504 公母插 (母)
NON-INSULATED FEMALE LUG

型號 ITEM NO.	T (mm)	單價
1.25-7A	0.8	1.1
2-7A	0.8	1.1
5.5-7A	0.8	1.4



1504 公母插保護套
FEMALE LUG COVER

型號 ITEM NO.	包裝	單價
CLV1-3A	100pcs	220
CLV1-5A	100pcs	240
CLV1-7A	100pcs	280



1504 旗型裸端子
FLAG FEMALE DISCONNECT

型號 ITEM NO.	T (mm)	單價
FL1.25-7A	0.8	2.4

適用1.25、2平方電線



1504 透明旗型絕緣套
VINYL FLAG SLEEVE

型號 ITEM NO.	包裝	單價
VTL2-7TR	100pcs	160

搭配FL1.25-7A 使用



1504 尼龍絕緣旗型端子
NYLON INSULATED FLAG FEMALE DISCONNECT

型號 ITEM NO.	T (mm)	單價
FLN1.25-7A	0.8	3.8
FLN2-7A	0.8	3.8



1504 透明絕緣套
VINYL SLEEVE

型號 ITEM NO.	包裝	單價
VT1-3TR	100pcs	80
VT2-5TR	100pcs	80
VT2-7TR	100pcs	90



1505 銅管端子
CABLE LUG

型號 ITEM NO.	單價
C2.5-5	5.5
C4-5	7.5
C6-5	7.5
C10-6	7.5
C10-8	7.5
C16-6	9.0
C16-8	9.0
C25-6	13.5
C25-8	13.5
C25-10	13.5
C35-6	19.5
C35-8	19.5
C35-10	19.5
C50-8	28.3
C50-10	28.3
C50-12	28.3
C70-8	43.0
C70-10	43.0
C70-12	43.0
C95-10	61.0
C95-12	61.0
C120-10	84.0
C120-12	84.0
C120-14	84.0
C120-16	84.0

型號 ITEM NO.	單價
C150-12	110.0
C150-14	110.0
C150-16	110.0
C185-12	148.0
C185-14	148.0
C185-16	148.0
C240-12	214.0
C240-14	214.0
C240-16	214.0
C240-18	214.0
C300-12	310.0
C300-14	310.0
C300-16	310.0
C300-18	310.0
C400-12	580.0
C400-14	580.0
C400-16	580.0
C400-18	580.0
C500-12	710.0
C500-14	710.0
C500-16	710.0
C500-18	710.0
C630-20	880.0
C630-22	880.0
C800-20	1300.0
C800-22	1300.0
C1000-20	1760.0
C1000-22	1760.0

● 電線稱呼對照表

Sq (台灣/日本)	AWG (美國)	Drahtgrobenbereich mm ² (英國)	DIN Querschnitt mm ² (德國)
0.5	26-22	0.1-0.4	0.14 / 0.20 / 0.25 / 0.36
1.25	22-16	0.4-1.0	0.5 / 0.75 / 1.0
2	16-14	1.1-2.6	1.5-2.5
2	16-14HD	1.1-2.6	1.5-2.5
5.5	12-10	2.7-6.6	4-6
8	8	6.7-10.5	10
14	6	10.6-16.7	16
22	4	16.8-26.6	25
38	2	26.7-42.4	35
60	1/0	42.5-60.5	50
70	2/0	60.6-76.2	70
80	3/0	76.3-97.0	95
100	4/0	98.0-120	120
150	250-300 mcm	121-151	150
180	300-350 mcm	152-192	185
200	400 mcm	193-242	240
325	500-600 mcm	243-304	300