







A  
B  
C  
D  
E  
F  
G

A  
B  
C  
D  
E  
F  
G



### SPECIFICATIONS

- 1.Voltage rating: 250V AC, DC
- 2.Current rating: 3A, AC, DC
- 3.Withstanding Voltage: 1000V AC/minute
- 4.Insulation resistance:800M min
- 5.Temperature range: -25 ° C-+85 ° C
- 6.Contact resistance: 20m max

### HOUSING

Housing Material:Nylon66 UL94V-0(2)  
 Accepts :T2029 terminal  
 Mates with: M2029 series header  
 Poles : 02-16P  
 Part No.: P2029-xx-N0

Pin位数

P/N	DIM A	DIM B	DIM C
2	2.0	6.0	4.5
3	4.0	8.0	6.5
4	6.0	10.0	8.5
5	8.0	12.0	10.5
6	10.0	14.0	12.5
7	12.0	16.0	14.5
8	14.0	18.0	16.5
9	16.0	20.0	18.5
10	18.0	22.0	20.5
11	20.0	24.0	22.5
12	22.0	26.0	24.5
13	24.0	28.0	26.5
14	26.0	30.0	28.5
15	28.0	32.0	30.5
16	30.0	34.0	32.5

WWW.XFCONN.COM

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	<b>XFCN</b> 兴飞连接器有限公司 CONNECTORS XFCN CONNECTORS CO., LTD.		SHEET	1/1
				X.	±0.30	X°	±5°			CHKD	DATE
				.X	±0.20	.X°	±2°	APPD	PRODUCT NAME	2.00mm Crimp Style Connectors	
				.XX	±0.08	.XX°	±1°	VIEW	PART. NO.	SCALE	1:1
				.XXX	±0.03	.XXX°	±0.5°			DWG NO.	009
A0 VER	MODIFICATION		DRAW	DATE							