




Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE ± 0.05)



SPECIFICATIONS
 Rated Current: 2.0AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 400V AC/DC
 Insulation Resistance: 800MΩ Min
 Operation Temperature: -40°C to +105°C

Contact Material: Brass
 Contact Plating: Au or Sn Over Ni
 Insulator Material: Polyester (UL94V-0)
 Resistance To Soldering Heat:
 245°C ± 5°C, 10s (PBT insulator)
 260°C ± 5°C, 10s (PA6T & PA9T & LCP insulator)



Ordering Information

HC-JN 200 - * - N - W - * - **

| | | | | |
|---|-------------------------|--------------------------------------|-----------------------------|--|
| No. of Rows 1=Single Row 2=Dual Row | No. of Pins 03-32Pin | Type 0=直插 1=弯针 2=直插 3=弯插 | Length (Plastic) (mm) | Contact Plating G0:Gold Flash G1:1u" Gold G2:3u" Gold G3:5u" Gold G4:10u" Gold G5:15u" Gold G6:30u" Gold S0:Gold Flash/Tin S1:Tin |
|---|-------------------------|--------------------------------------|-----------------------------|--|

| | | | | | | | | | |
|-----|----------------|-------------|-------------------|---------|---|--------------|-----------------------|-----|----|
| | | | GENERAL TOLERANCE | 制图 | 深圳市华灿天禄电子有限公司 ShenzhenhuaciantianluELECTRONICS CO., LTD | | | | |
| | | | DIM TOL | DRAWING | | | | | |
| | | | X.X ± 0.30 | 审核 | 产品名称 | 筒牛2.00 双排 弯针 | 版本 | A | |
| | | | X.XX ± 0.20 | 批准 | APPROVAL | 标题 | REV. | | |
| | | | X.XXX ± 0.10 | 比例 | SCALE | 产品料号 | HC-JN200-2-N-W-5.7-XX | 单位 | mm |
| 序号 | 变更内容 | 日期 | Angle ± 3.0° | 投影 | Projection | 材料 | 页次 | 1/1 | |
| No. | MODIFY CONTENT | MODIFY DATE | | | | MATERIAL | SHEET | | |