



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

SPECIFICATIONS
 Rated Current:1.5AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:400V AC/DC
 Insulation Resistance:800MΩ Min
 Operation Temperature:-40°c to +105°c

Contact Material:Brass
 Contact Plating:Au or Sn Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)

Ordering Information

HC-JN 200 - * - N - Z - * - **

No. of Rows 1=Single Row 2=Dual Row	No. of Pins 1=40Pin 2=40Pin	Type Z=直针 N=弯针 S=插针 W=插针	Length (Plastic) (mm)	Contact Plating C0:Gold Flash G1:1u" Gold G2:3u" Gold G3:5u" Gold G4:10u" Gold G5:15u" Gold G6:30u" Gold S0:Gold Flash/Tin S1:Tin
---	-----------------------------------	--------------------------------------	-----------------------------	--

			GENERAL TOLERANCE		制图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD					
			DIM	TOL	审核 CHECK							
			X.X	±0.30	批准 APPROVAL		产品名称 TITLE		简牛2.00 双排 排母 直针		版本 REV.	A
			X.XX	±0.20	比例 SCALE		产品料号 PART NO.		HC-JN200-2-N-Z-5.7-XX		单位 UNITS	mm
			X.XXX	±0.10	投影 Projection		材料 MATERIAL				页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°									