




SECTION A-A



公差参数

Poles	Dim	Dim P	Dim L
2-6P		±0.10	±0.20
7-12P		±0.20	±0.30
13-18P		±0.25	±0.40
19-24P		±0.30	±0.50



PCB LAYOUT

材料及电镀

- ①. 塑件主体: PA66, UL94V-0
- ②. 焊 针: 黄铜, 镀镍

电气性能

- 额定电压: 300V
- 额定电流: 15A
- 接触电阻: 20mΩ (Max)
- 绝缘电阻: 500MΩ \DC500V
- 耐 电 压: AC2000V\1Min

机械性能

- 温度范围: -40℃ ~ +105℃
- 瞬时温度: +250℃ ,5秒

Ordering Information

HC2EDG * * - * - NP - *

Type	款式-开口	Pitch	No. of Poles	Colour
直插式	弯插式	2.54=2.54mm	2-24Pin	V=Green
直插式	弯插式	3.5=3.50mm	2P=2Pin	L=Bluc
		3.81=3.81mm	3P=3Pin	O=Orange
		5.08=5.08mm	R=Red
		7.62=7.62mm		B=Black
				OR=Gray

			GENERAL TOLERANCE	制图	深圳市华灿天禄电子有限公司			
			DIM TOL	DRAWING	ShenzhenhuacantianluELECTRONICS CO., LTD			
			X.X ±0.50	审核	产品名称	5.08 单排 插拔式 接线端子	版本	A
			X.XX ±0.30	CHECK	TITLE	开口 弯针	REV.	
			X.XXX ±0.10	批准	产品料号	HC2EDGR-5.08-NP-V	单位	mm
			Angle ±3.0°	APPROVAL	PART NO.		UNITS	
序号	变更内容	日期	投影	投影	材料		页次	1/1
No.	MODIFY CONTENT	MODIFY DATE	Projection	Projection	MATERIAL		SHEET	