



SECTION A-A

材料及电镀
 ①.塑件主体: PA66, UL94V-0
 ②.焊 针: 黄铜, 镀镍


电气性能
 额定电压: 300V
 额定电流: 15A
 接触电阻: 20mΩ (Max)
 绝缘电阻: 500MΩ\DC500V
 耐 电 压: AC2000V\1Min

机械性能
 温度范围: -40℃ ~ +105℃
 瞬时温度: +250℃, 5秒



公差参数

| Poles | Dim | Dim P | Dim L |
|--------|-------|-------|-------|
| 2-6P | ±0.10 | ±0.20 | ±0.20 |
| 7-12P | ±0.20 | ±0.30 | ±0.30 |
| 13-18P | ±0.25 | ±0.40 | ±0.40 |
| 19-24P | ±0.30 | ±0.50 | ±0.50 |



PCB LAYOUT

Ordering Information

XD2EDG

* * - * - NP - *

Type
 V=直针
 R=弯针
 K=插座

款式-开口
 C=封底
 M=螺纹

PITCH
 2.54=2.54mm
 3.5=3.5mm
 3.81=3.81mm
 5.08=5.08mm
 7.62=7.62mm

No. of Pins
 2-24 Pin
 26-27Pin
 3P=3Pin

Colour
 V=Green
 r=Blue
 C=Orange
 R=Red
 B=Black
 GR=Gray

| | | | | | | | | |
|-----------|------------------------|-------------------|-------------------|------------------|---|------------------|-------------|-----|
| | | | GENERAL TOLERANCE | 制图 DRAWING | 深圳讯答科技有限公司 ShenzhenXundaTechnology Co.,Ltd | | | |
| | | | DIM TOL | 审核 CHECK | | | | |
| | | | X.X ±0.30 | 批准 APPROVAL | 产品名称 TITLE | 5.08 单排 插拔式 接线端子 | 版本 REV. | A |
| | | | X.XX ±0.20 | 比例 SCALE | 产品料号 PART NO. | 开口 弯针 | 单位 UNITS | mm |
| | | | X.XXX ±0.10 | 投影 Projection | 材料 MATERIAL | | 页次 SHEET | 1/1 |
| 序号 No. | 变更内容 MODIFY CONTENT | 日期 MODIFY DATE | Angle ±3.0° | | | | | |