

SECTION A-A




材料及电镀
 ①.塑件主体: PA66, UL94V-0
 ②.焊 针: 黄铜, 镀镍

电气性能
 额定电压: 150V
 额定电流: 5A
 接触电阻: 20mΩ (Max)
 绝缘电阻: 500MΩ\DC1000V
 耐 电 压: AC1300V\1Min
 使用线径: 26-20AWG 0.2-0.5mm²

机械性能
 温度范围: -40℃ ~ +105℃
 瞬时温度: +250℃ 5秒

公差参数

| Poles | Dim | Dim P | Dim L |
|--------|-----|-------|-------|
| 2-6P | | ±0.10 | ±0.15 |
| 7-12P | | ±0.20 | ±0.20 |
| 13-18P | | ±0.25 | ±0.30 |
| 19-24P | | ±0.30 | ±0.40 |



Ordering Information

XD2EDG * * - * - NP - *

| | | | | |
|------|------|-------------|------------|----------|
| Type | C=封带 | PITCH | No.of Pins | Colour |
| V=直插 | | 2.54±2.54mm | 2-24 Pin | V=Green |
| R=弯插 | | 3.5±3.50mm | 2P~2Pn | L=Blue |
| K=插座 | | 3.81±3.81mm | 3P~3Pn | O=Orange |
| | | 5.08±5.08mm | | R=Red |
| | | 7.62±7.62mm | | B=Black |
| | | | | GR=Gray |

| | | | | | | | | |
|-----------|------------------------|-------------------|-------------------|------------------|--|--------------------------|-------------|-----|
| | | | GENERAL TOLERANCE | 制图 DRAWING | 深圳讯答科技有限公司 ShenzhenXundaTechnology Co.,Ltd | | | |
| | | | DIM TOL | 审核 CHECK | | | | |
| | | | X.X ±0.30 | 批准 APPROVAL | 产品名称 TITLE | 2.54 单排 插拔式 接线端子 封闭弯针 | 版本 REV. | A |
| | | | X.XX ±0.20 | 比例 SCALE | 产品料号 PART NO. | XD2EDGRC-2.54-NP-V | 单位 UNITS | mm |
| | | | X.XXX ±0.10 | 投影 Projection | 材料 MATERIAL | | 页次 SHEET | 1/1 |
| | | | Angle ±3.0° | | | | | |
| 1 | 初版发行 | | | | | | | |
| 序号 No. | 变更内容 MODIFY CONTENT | 日期 MODIFY DATE | | | | | | |