

SECTION A-A


材料及电镀  
 ①.塑件主体: PA66, UL94V-0  
 ②.焊 针: 黄铜, 镀镍

电气性能  
 额定电压: 300V  
 额定电流: 15A  
 接触电阻: 20mΩ (Max)  
 绝缘电阻: 500MΩ/DC500V  
 耐 电 压: AC2000V\1Min

机械性能  
 温度范围: -40℃ ~ +105℃  
 瞬时温度: +250℃, 5秒

公差参数

Point	Dim	Dim P	Dim L
2-6P		±0.10	±0.20
7-12P		±0.20	±0.30
13-18P		±0.25	±0.40
19-24P		±0.30	±0.50



**Ordering Information**

XD2EDG \* \* - \* - NP - \*

Type	默认=开口	PITCH	No. of Pins	Colour
V=直插	C=前插	2.54*2.54mm	2-24 Pin	V=Green
R=弯插	A=侧插	3.5*3.50mm	2*2Pin	L=Blue
K=母座		3.81*3.81mm	3*3Pin	O=Orange
		5.08*5.08mm	.....	R=Red
		7.62*7.62mm		B=Black
				GR=Gray

			GENERAL TOLERANCE	制 图 DRAWING	<b>深圳讯答科技有限公司</b> ShenzhenXundaTechnology Co.,Ltd			
			DIM TOL	审 核 CHECK				
			X.X ±0.30	批 准 APPROVAL	产品名称 TITLE	5.08 单排 插拔式 接线端子	版本 REV.	A
			X.XX ±0.20	比 例 SCALE	产品料号 PART NO.	XD2EDGRC-5.08-NP-V	单 位 UNITS	mm
			X.XXX ±0.10	投 影 Projection	材 料 MATERIAL		页 次 SHEET	1/1
			Angle ±3.0°					
1	初版发行							
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						