



SECTION A-A

材料及电镀
 ①.塑件主体: PA66, UL94V-0
 ②.焊 针: 黄铜, 镀镍


电气性能
 额定电压: 150V
 额定电流: 5A
 接触电阻: 20mΩ (Max)
 绝缘电阻: 500MΩ\DC1000V
 耐 电 压: AC1300V\1Min
 使用线径: 26-20AWG 0.2-0.5mm²

机械性能
 温度范围: -40°C ~ +105°C
 瞬时温度: +250°C 5秒



公差参数

Poles	Dim	Dim P	Dim L
2-6P		±0.10	±0.20
7-12P		±0.20	±0.30
13-18P		±0.25	±0.40
19-24P		±0.30	±0.50



Ordering Information

XD2EDG * * - * - NP - *

Type	C=排距	PITCH	No.of Pins	Colour
V=直针		2.54~2.54mm	2-24 Pin	V=Green
R=弯针		3.5~3.50mm	2~24 Pin	L=Blue
K=母座		3.81~3.81mm	2~2Pin	O=Orange
		5.08~5.08mm	3~3Pin	R=Red
		7.62~7.62mm	B=Black
				GR=Gray

			GENEAL TOLERANCE	制 图 DRAWING	深圳讯答科技有限公司 ShenzhenXundaTechnology Co.,Ltd			
			DIM TOL	审 核 CHECK	产品名称 TITLE	2.54 单排 插拔式 接线端子 封闭 直针	版 本 REV.	A
			X.X ±0.30	批 准 APPROVAL	产品料号 PART NO.	XD2EDGVC-2.54-NP-V	单 位 UNITS	mm
			X.XX ±0.20	比 例 SCALE	材 料 MATERIAL		页 次 SHEET	1/1
			X.XXX ±0.10	投 影 Projection				
			Angle ±3.0°					
1	初版发行							
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						