



3 Pin以上

2 Pin

公差参数

| Notes  | Dim | Dim P | Dim L |
|--------|-----|-------|-------|
| 2-6P   |     | ±0.10 | ±0.20 |
| 7-12P  |     | ±0.20 | ±0.30 |
| 13-18P |     | ±0.25 | ±0.40 |
| 19-24P |     | ±0.30 | ±0.50 |

材料及电镀  
 ① 螺 丝: M2.5, 钢, 镀锌, 一字槽  
 ② 塑件主体: PA66, UL94V-0  
 ③ 夹 子: 磷青铜, 镀镍  
 ④ 方 盒: 黄铜, 镀镍  
 ⑤ 塑件盖板: PA66, UL94V-0

电气性能  
 额定电压: 300V  
 额定电流: 15A  
 接触电阻: 20mΩ (Max)  
 绝缘电阻: 500MΩ \DC500V  
 耐 电 压: AC2000V\1Min  
 使用线径: 28-14AWG 2.5mm<sup>2</sup>

机械性能  
 温度范围: -40℃ ~ +105℃  
 瞬时温度: +250℃ 5秒  
 扭 力: 0.5Nm (4.43lbin)  
 剥线长度: 7-8mm

**Ordering Information**

HC2EDG \* \* - \* - NP - \*

|                                 |                        |   |   |  |
|---------------------------------|------------------------|---|---|--|
| Type<br>V: 直插<br>M: 带耳<br>H: 带钩 | 取法: 开孔<br># 间距<br># 螺距 | PITCH<br>2.54=2.54mm<br>3.5=3.50mm<br>3.81=3.81mm<br>5.08=5.08mm<br>7.62=7.62mm | No.of<br>Pins<br>2-24Pin<br>2P=2Pin<br>3P=3Pin<br>..... | Colour<br>V=Green<br>L=Bluc<br>O=Orange<br>R=Red<br>B=Black<br>GR=Gray |
|---------------------------------|------------------------|---|---|--|

|           |                        |                   |                  |       |                   |  |   |                            |              |     |
|-----------|------------------------|-------------------|------------------|-------|-------------------|--|---|----------------------------|--------------|-----|
|           |                        |                   | GENREL TOLERANCE |       | 制 图<br>DRAWING    |  | 深圳市华灿天禄电子有限公司<br>ShenzhenhuacantianluELECTRONICS CO., LTD |                            |              |     |
|           |                        |                   | DIM              | TOL   | 审 核<br>CHECK      |  |   |                            |              |     |
|           |                        |                   | X. X             | ±0.50 | 批 准<br>APPROVAL   |  | 产品名称<br>TITLE   | 5.08 单排 插拔式 带螺丝<br>接线端子 母座 | 版本<br>REV.   | A   |
| 1         |                        |                   | 初版发行             |       | 比 例<br>SCALE      |  | 产品料号<br>PART NO.  | HC2EDGKM-5.08-NP-V         | 单 位<br>UNITS | mm  |
| 序号<br>No. | 变更内容<br>MODIFY CONTENT | 日期<br>MODIFY DATE | Angle ±3.0°      |       | 投 影<br>Projection |  | 材 料<br>MATERIAL   |                            | 页 次<br>SHEET | 1/1 |