

SECTION A-A

材料及电镀



- ①. 塑件主体: PA66, UL94V-0
- ②. 焊 针: 黄铜, 镀镍

电气性能

- 额定电压: 150V
- 额定电流: 5A
- 接触电阻: 20mΩ (Max)
- 绝缘电阻: 500MΩ \DC1000V
- 耐 电 压: AC1300V\1Min
- 使用线径: 26-20AWG 0.2-0.5mm<sup>2</sup>


机械性能

- 温度范围: -40℃ ~ +105℃
- 瞬时温度: +250℃ 5秒




公差参数

Poles	Dim	Dim P	Dim L
2-6P		±0.10	±0.15
7-12P		±0.20	±0.20
13-18P		±0.25	±0.30
19-24P		±0.30	±0.40



Ordering Information



			GENERAL TOLERANCE	制图	深圳市华灿天禄电子有限公司			
			DIM TOL	DRAWING	ShenzhenhuacantianluELECTRONICS CO., LTD			
			X.X ±0.50	审核	产品名称	2.54 单排 插拔式 接线端子	版本	A
			X.XX ±0.30	CHECK	TITLE	封闭 弯针	REV.	
			X.XXX ±0.10	批准	产品料号	HC2EDGRC-2.54-NP-V	单位	mm
			Angle ±3.0°	APPROVAL	PART NO.		UNITS	
序号	变更内容	日期	投影	投影	材料		页次	1/1
No.	MODIFY CONTENT	MODIFY DATE	Projection	Projection	MATERIAL		SHEET	