



**SPECIFICATIONS**

- 1、 Current Rating: 3A AC, DC
- 2、 Voltage Rating: 250V AC, DC
- 3、 Temperature Range: -40°C ~ +105°C
- 4、 Contact Resistance: 20mΩ Max
- 5、 Insulation Resistance: 1000mΩ Min
- 6、 Withstanding Voltage: 1000V AC/minute
- 7、 Material: Wafer Nylon66 UL94-V0(2)  
PIN Brass Tin-plated

Circuit	Part NO.	Dimensions mm		
		A	B	C
2	HC-XHB-2A-05	2.50	7.50	6.00
3	HC-XHB-3A-05	5.00	10.00	8.50
4	HC-XHB-4A-05	7.50	12.50	11.00
5	HC-XHB-5A-05	10.00	15.00	13.50
6	HC-XHB-6A-05	12.50	17.50	16.00
7	HC-XHB-7A-05	15.00	20.00	18.50
8	HC-XHB-8A-05	17.50	22.50	21.00
9	HC-XHB-9A-05	20.00	25.00	23.50
10	HC-XHB-10A-05	22.50	27.50	26.00
11	HC-XHB-11A-05	25.00	30.00	28.50
12	HC-XHB-12A-05	27.50	32.50	31.00
13	HC-XHB-13A-05	30.00	35.00	33.50
14	HC-XHB-14A-05	32.50	37.50	36.00
15	HC-XHB-15A-05	35.00	40.00	38.50

**Ordering Information**

HC-XHB - N\*\*\* - \* - 05

Pin Type Colour  
 1-05 1-05 1-05  
 2-05 2-05 2-05  
 3-05 3-05 3-05  
 4-05 4-05 4-05  
 5-05 5-05 5-05  
 6-05 6-05 6-05  
 7-05 7-05 7-05  
 8-05 8-05 8-05  
 9-05 9-05 9-05  
 10-05 10-05 10-05  
 11-05 11-05 11-05  
 12-05 12-05 12-05  
 13-05 13-05 13-05  
 14-05 14-05 14-05  
 15-05 15-05 15-05

GENERAL TOLERANCE			制 图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
	DIM	TOL	审 核 CHECK	产品名称 TITLE	XHB (2.50)单排带扣 直针	版本 REV.	A
	X.X	±0.30	批 准 APPROVAL	产品料号 PART NO.	HC-XHB-NA-BR-05	单 位 UNITS	mm
1	初版发行		比 例 SCALE	材 料 MATERIAL		页 次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°	投 影 Projection			