

公差参数

Poles	Dim	Dim P	Dim L
2-6P		±0.10	±0.15
7-12P		±0.20	±0.20
13-18P		±0.25	±0.30
19-24P		±0.30	±0.40

材料及电镀

- ①. 螺 丝: M1.6, 钢, 镀锌, 一字槽
- ②. 塑件主体: PA66, UL94V-0
- ③. 夹 子: 磷青铜, 镀镍
- ④. 方 盒: 黄铜, 镀镍
- ⑤. 塑件盖板: PA66, UL94V-0


电气性能

额定电压: 150V
 额定电流: 5A
 接触电阻: 20mΩ (Max)
 绝缘电阻: 500MΩ \DC1000V
 耐 电 压: AC1300V\1Min
 使用线径: 26-20AWG 0.2-0.5mm²

机械性能

温度范围: -40℃ ~ +105℃
 瞬时温度: +250℃ 5秒
 扭 力: 0.1Nm (0.89Lbin)
 剥线长度: 5-6mm

Ordering Information



			GENEERL TOLERANCE	制 图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM TOL	审 核 CHECK	产品名称 TITLE	2.54 单排 插拔式 封闭 接线端子 母座	版本 REV.	A
			X.X ±0.50	批 准 APPROVAL	产品料号 PART NO.	HC2EDGK-2.54-NP-V	单 位 UNITS	mm
			X.XX ±0.30	比 例 SCALE	材 料 MATERIAL		页 次 SHEET	1/1
			X.XXX ±0.10	投 影 Projection				
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°					