



公差参数

| Poles  | Dim | Dim P | Dim L |
|--------|-----|-------|-------|
| 2-6P   |     | ±0.10 | ±0.15 |
| 7-12P  |     | ±0.20 | ±0.20 |
| 13-18P |     | ±0.25 | ±0.30 |
| 19-24P |     | ±0.30 | ±0.40 |

材料及电镀  
 ①.螺 丝: M1.6, 钢, 镀锌, 一字槽  
 ②.塑件主体: PA66, UL94V-0  
 ③.夹 子: 磷青铜, 镀镍  
 ④.方 盒: 黄铜, 镀镍  
 ⑤.塑件盖板: PA66,UL94V-0

电气性能  
 额定电压: 150V  
 额定电流: 5A  
 接触电阻: 20mΩ (Max)  
 绝缘电阻: 500MΩ\DC1000V  
 耐 电 压: AC1300V\1Min  
 使用线径: 26-20AWG 0.2-0.5mm<sup>2</sup>

机械性能  
 温度范围: -40°C ~ +105°C  
 瞬时温度: +250°C 5秒  
 扭 力: 0.1Nm(0.89Lbin)  
 剥线长度: 5-6mm

Ordering Information

XD2EDG \* \* - \* - NP - \*

|      |       |             |            |          |
|------|-------|-------------|------------|----------|
| Type | M=带螺钉 | Pitch       | No.of Pins | Colour   |
| V=直插 |       | 2.54*2.54mm | 2-24 Pins  | Y=Green  |
| R=带针 |       | 3.5*3.50mm  | 2-24 Pins  | L=Blue   |
| K=带孔 |       | 3.81*3.81mm | 2P~2Pn     | O=Orange |
|      |       | 5.08*5.08mm | 3P~3Pn     | R=Red    |
|      |       | 7.62*7.62mm | .....      | B=Black  |
|      |       |             |            | GR=Gray  |

|           |                        |                   |                  |                   |  |                         |              |     |
|-----------|------------------------|-------------------|------------------|-------------------|--|-------------------------|--------------|-----|
|           |                        |                   | GENEAL TOLERANCE | 制 图<br>DRAWING    | <b>深圳讯答科技有限公司</b><br>ShenzhenXundaTechnology Co.,Ltd |                         |              |     |
|           |                        |                   | DIM TOL          | 审 核<br>CHECK      |  |                         |              |     |
|           |                        |                   | X.X ±0.30        | 批 准<br>APPROVAL   | 产品名称<br>TITLE  | 2.54单排 插拔式 封闭<br>接线端子母座 | 版 本<br>REV.  | A   |
|           |                        |                   | X.XX ±0.20       | 比 例<br>SCALE      | 产品料号<br>PART NO.                                     | XD2EDGK-2.54-NP-V       | 单 位<br>UNITS | mm  |
|           |                        |                   | X.XXX ±0.10      | 投 影<br>Projection | 材 料<br>MATERIAL                                      |                         | 页 次<br>SHEET | 1/1 |
|           |                        |                   | Angle ±3.0°      |                   |  |                         |              |     |
| 1         | 初版发行                   |                   |                  |                   |  |                         |              |     |
| 序号<br>No. | 变更内容<br>MODIFY CONTENT | 日期<br>MODIFY DATE |                  |                   |  |                         |              |     |