



公差参数

Poles	Dim	Dim P	Dim L
2-6P		±0.10	±0.15
7-12P		±0.20	±0.20
13-18P		±0.25	±0.30
19-24P		±0.30	±0.40

材料及电镀  
 ①.螺 丝: M1.6, 钢, 镀锌, 一字槽  
 ②.塑件主体: PA66, UL94V-0  
 ③.夹 子: 磷青铜, 镀镍  
 ④.方 盒: 黄铜, 镀镍  
 ⑤.塑件盖板: PA66,UL94V-0

电气性能  
 额定电压: 150V  
 额定电流: 5A  
 接触电阻: 20mΩ (Max)  
 绝缘电阻: 500MΩ\DC1000V  
 耐 电 压: AC1300V\1Min  
 使用线径: 26-20AWG 0.2-0.5mm<sup>2</sup>

机械性能  
 温度范围: -40°C ~ +105°C  
 瞬时温度: +250°C 5秒  
 扭 力: 0.1Nm(0.89Lbin)  
 剥线长度: 5-6mm

**Ordering Information**

XD2EDG \* \* - \* - NP - \*

Type	M=带螺钉	Pitch	No.of Pins	Colour
V=直插		2.54*2.54mm	2-24 Pins	Y=Green
R=带针		3.5*3.50mm	2-24 Pins	L=Blue
K=带盖		3.81*3.81mm	2P~2Pn	O=Orange
		5.08*5.08mm	3P~3Pn	R=Red
		7.62*7.62mm	.....	B=Black
				GR=Gray

			GENEAL TOLERANCE		制 图 DRAWING		<b>深圳讯答科技有限公司</b> ShenzhenXundaTechnology Co.,Ltd					
			DIM TOL		审 核 CHECK							
			X.X ±0.30		批 准 APPROVAL		产品名称 TITLE		2.54单排 插拔式 封闭 接线端子母座		版 本 REV.	A
			X.XX ±0.20		比 例 SCALE		产品料号 PART NO.		XD2EDGK-2.54-NP-V		单 位 UNITS	mm
			X.XXX ±0.10		投 影 Projection		材 料 MATERIAL				页 次 SHEET	1/1
1	初版发行		日期 MODIFY DATE									
序号 No.	变更内容 MODIFY CONTENT											