



公差参数

Poles	Dim	Dim P	Dim L
2-6P		±0.10	±0.15
7-12P		±0.20	±0.20
13-18P		±0.25	±0.30
19-24P		±0.30	±0.40

材料及电镀
 ①.螺 丝: M1.6, 钢, 镀锌, 一字槽
 ②.塑件主体: PA66, UL94V-0
 ③.夹 子: 磷青铜, 镀镍
 ④.方 盒: 黄铜, 镀镍
 ⑤.塑件盖板: PA66,UL94V-0

电气性能
 额定电压: 150V
 额定电流: 5A
 接触电阻: 20mΩ (Max)
 绝缘电阻: 500MΩ\DC1000V
 耐 电 压: AC1300V\1Min
 使用线径: 26-20AWG 0.2-0.5mm²

机械性能
 温度范围: -40°C ~ +105°C
 瞬时温度: +250°C 5秒
 扭 力: 0.1Nm(0.89Lbin)
 剥线长度: 5-6mm

Ordering Information

XD2EDG * * - * - NP - *

Type	M=带螺钉	Pitch	No.of Pins	Colour
V=直插		2.54*2.54mm	2-24 Pins	Y=Green
R=带针		3.5*3.50mm	2-24 Pins	L=Blue
K=带孔		3.81*3.81mm	2P~2Pn	O=Orange
		5.08*5.08mm	3P~3Pn	R=Red
		7.62*7.62mm	B=Black
				GR=Gray

			GENERAL TOLERANCE		制图 DRAWING		深圳讯答科技有限公司 ShenzhenXundaTechnology Co.,Ltd					
			DIM TOL		审核 CHECK							
			X.X ±0.30		批准 APPROVAL		产品名称 TITLE		2.54单排 插拔式 封闭 接线端子母座		版本 REV.	A
			X.XX ±0.20		比例 SCALE		产品料号 PART NO.		XD2EDGK-2.54-NP-V		单 位 UNITS	mm
			X.XXX ±0.10		投影 Projection		材 料 MATERIAL				页 次 SHEET	1/1
1	初版发行		日期 MODIFY DATE									
序号 No.	变更内容 MODIFY CONTENT		日期 MODIFY DATE									