









CS-1149-02BV0W (0104)



CS-1149-06EV0W (0104)




■ SPECIFICATIONS

- Voltage rating: 250V AC, DC
- Current rating: 7A-9A, AC, DC
- Withstanding voltage: 1500V AC/minute
- Insulation resistance: 1000MΩ min
- Temperature range: -40°C to +105°C
- Contact resistance: 20mΩ max

■ HOUSING

- Part No.: CS-1149-06EV0W (0104)
CS-1149-02BV0W (0104)
- Poles: 06+02
- Material: Nylon 66, UL94V-0, 白色0104
- Color: White
- Q' TY: 1000 pcs/bag

料号区分示意图



RoHS 2.0

本圖紙知識產權及版權由永丰盈有限公司所有, 未經書面許可不准擅自傳閱、复制和修改. 本公司保留法律追究的权利.	类别	HOUSING	品名	CS-1149-06EV0W (0104) + 02BV0W (0104)			材料		单位	mm	SHEET 1 OF 1	
	版本	A/0	设计	李文畅	X.X	±0.40	颜色		比例	1:1	▲	修改内容
	制定部门	工程课	绘制	李文畅	X.XX	±0.30	画法		数量		①	
	工程图号	CS-1149	审核	姚培柱	X.XXX	±0.20	深圳市永丰盈电子有限公司 ShenZhenYongFengYing ELECTRONICS CO., LTD.				②	
	制定日期	2023-07-05	核准	周中湖	X.XXXX	±0.10						③