









CS-1149-02BV2R (0068)



CS-1149-06EV2R (0068)



CS-1149-06EV2R (0068)+02BV2R (0068) 组合图


■ SPECIFICATIONS

- Voltage rating: 250V AC,DC
- Current rating: 7A-9A, AC,DC
- Withstanding voltage: 1500V AC/minute
- Insulation resistance:1000MΩ min
- Temperature range:-40°C to +105°C
- Contact resistance:20mΩ max

■ HOUSING

- Part No. :CS-1149-06EV2R (0068)
CS-1149-02BV2R (0068)
- Poles:06+02
- Material:Nylon 66, UL94V-2, 红色0068
- Color:Red
- Q' TY:1000 pcs/bag

料号区分示图



RoHS 2.0

本圖紙知識產權及版權由永丰盈有限公司所有,未經書面許可不准擅自傳閱、复制和修改.本公司保留法律追究的权利.

类别	HOUSING	品名	CS-1149-06EV2R (0068) +02BV2R (0068)		
版本	A/0	设计	李文畅	X.X	±0.40
制定部门	工程课	绘制	李文畅	X.XX	±0.30
工程图号	CS-1149	审核	姚培柱	X.XXX	±0.20
制定日期	2023-07-05	核准	周中湖	X.XXXX	±0.10

材料		单位	mm
颜色		比例	1:1
画法		数量	
CST 深圳市永丰盈电子有限公司		ShenZhenYongFengYing ELECTRONICS CO.,LTD.	

SHEET 1 OF 1		
	修改内容	修改日期