



Click [here](#) for the 3D model.

### Dimensions

D	45mm NOM
L	79.5mm NOM

### Packaging Specifications

Typical Component Weight	400
Packaging	Bulk Tray, Box
Packaging Quantity	30

### General Information

Style	Bolt-On
Description	Langevin Bolt-On Transducers
RoHS	With Exemptions
SCIP Number	6629125f-50d3-4e75-ae76-25e0bc1955b0
Notes	Horn construction; output surface has step or horn shape.

### Specifications

Series	NBL
Capacitance	4000 pF
Resonant Frequency	28 kHz
Dynamic Admittance	40 mS
Mechanical Q	500 Qm
Allowable Velocity	40 cm/S
Allowable Power	50
Temperature Range	-40/+120°C