

# OWR-081525L-32B

## Wideband receiver

Optimized for wideband. HAC compatible. For mobile application



### Characteristics

Size (LxWxH) [mm]	15.0x8.0x3.1	
Sensitivity [dB SPL]	92.5±3dB	[dB SPL @1kHz, 15mW, 1cm]
Impedance [Ω]	32	
Power [W]	15.0 / 20.0	Free field
F0 [Hz]	320	Free field
Termination	Leaf spring	

Specifications are subject to change without prior notice. Upon request Ole Wolff can supply further specifications, simulation parameters etc.

### Mechanical drawing

