

84695-1 ✓ ACTIVE

Dynamic Series | Dynamic 5000 Series

TE Internal #: 84695-1

Tab Contact, Gold, 12 – 10 AWG Wire Size, 3.08 – 5.5 mm² Wire Size, Power, -67 – 221 °F [-55 – 105 °C], Dynamic 5000 Series

[View on TE.com >](#)



Connectors > Contacts > Connector Contacts > Contact: Component To Wire ; 20-45A ; 20-8 wire size



Contact Type: **Tab**

Contact Mating Area Plating Material: **Gold**

Wire Size: **3.08 – 5.5 mm²**

Product Terminates To: **Wire & Cable**

[All Contact: Component To Wire ; 20-45A ; 20-8 wire size \(43\)](#)

Features

Contact Features

Mating Tab Width	6.4 mm[.25 in]
Mating Tab Thickness	1 mm[.039 in]
Contact Type	Tab
Contact Mating Area Plating Material	Gold
Contact Current Rating (Max)	30 A

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Dimensions

Wire Size	3.08 – 5.5 mm ²
-----------	----------------------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------



Packaging Features

Packaging Method	Reel & Box
------------------	------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 <p>TE Part # 2151086-2 OCEAN_2.0_APPLICATOR-S-160F240F</p>	 <p>TE Part # 7-2151086-2 OCEAN_2.0_APPLICATOR-S-160F240F</p>	 <p>TE Part # 7-2151086-7 OCEAN_2.0_SPARE_PART_KIT-160F240F</p>
--	---	--


Also in the Series | [Dynamic 5000 Series](#)




Connector Caps & Covers(2)



Connector Contacts(43)




Connector Hardware(3)




Insertion & Extraction Tools(1)



PCB Headers & Receptacles(59)



PCB Terminal Blocks(6)



Wire-to-Board Connector Assemblies & Housings(71)

Customers Also Bought



TE Part #2-1827864-0
DYNAMIC 1200D REC HSG 20P Y
BLACK



TE Part #1-179553-2
DYNAMIC D-3200S TAB HSG 2P K/X




TE Part #1-353047-3
DYNAMIC D-5200S TAB HSG 3P K/X



TE Part #917802-2
Contact: Component To Wire ; 20-
45A ; 20-8 wire size



TE Part #2316815-2
HD3 TAB CONTACT AU0.38 M SIZE



TE Part #7-1447183-6
FSN-2.5A-11-1 (SPECIAL BENDING)

Documents

Product Drawings

D5000 TAB CONT M LONG REEL AU PLATING

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_84695-1_H.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_84695-1_H.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_84695-1_H.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1-1773732-4_DYNAMIC_SERIES_CATALOG_ENGLISH](#)

Japanese

[1-1773732-4_DYNAMIC_SERIES_CATALOG_ENGLISH](#)

English

Product Specifications

[Crimping of D-5000 Contacts For High Current Hybrid Drawer Connector](#)

English

[Application Specification](#)

English

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English

[Extraction Tool for AMP Dynamic D-5000 Series](#)

English

Agency Approvals

[TUV Certificate](#)

English

[TUV Certificate](#)

English