



General Information

| | |
|----------------|---|
| Series | M4 |
| Style | Sheet |
| Description | Flex Suppressor Halogen Free Type |
| Features | High Magnetic Permeability Type, Low Magnetic Loss Type |
| RoHS | Yes |
| Qualifications | UL94 HB, UL File No. E176124 |
| Environment | Halogen Free, PVC Free, Lead Free, Red Phosphorus Free |

Specifications

| | |
|---------------------|---------------------|
| Temperature Range | -40/+105°C |
| Permeability | 40 u At 13.56MHz |
| Effective Frequency | 13.56 MHz and below |
| Specific Gravity | 3.1 TYP |
| Surface Resistivity | 10 MOhm/sq. TYP |

Dimensions

| | |
|------------|-------------|
| Sheet Size | 240mmx30M |
| L | 30000mm NOM |
| W | 240mm NOM |
| T | 0.2mm NOM |

Packaging Specifications

| | |
|--------------------------|------------------|
| Tape Description | No Adhesive Tape |
| Typical Component Weight | 4176.25 g |