


ATM_ID Equivalent - Low Voltage, Fast Acting, Miniature Automotive with LED Indicator


Features

- Long Life (1000 hrs min.) LED Indicator lights when fuse is blown
- Miniature Blade Type
- RoHS Compliant



NTE Type No.	Rated Current	Color Code	Diag No.
74-LMAF3A	3A	Violet	F-12
74-LMAF5A	5A	Tan	F-12
74-LMAF7.5A	7.5A	Brown	F-12
74-LMAF10A	10A	Red	F-12
74-LMAF15A	15A	Blue	F-12
74-LMAF20A	20A	Yellow	F-12
74-LMAF25A	25A	Natural	F-12
74-LMAF30A	30A	Green	F-12

F-12



Specifications

Rated Voltage: 32V

LED Voltage Rating: 12VDC, 24VDC, 32VDC

LED Lifetime: around 1000 hours at +60°C. The resin won't be melted under +130°C.

Time Current Characteristics:

% of Ampere Rating	Opening Time
110%	100 hours min.
135%	0.75 – 1800 seconds
200%	0.15 – 5 seconds
350%	0.08 – 0.25 seconds


Accessories:

Description	NTE Type No.
In-Line Fuse Holder, up to 15A	74-IFHMA15
In-Line Fuse Holder, up to 30A	74-IFHMA30
In-Line Fuse Holder w/LED Light, up to 15A	74-IFHMAL15
In-Line Fuse Holder w/LED Light, up to 30A	74-IFHMAL30

ATC_ID Equivalent - Low Voltage, Fast Acting, Automotive with LED Indicator


Features

- Long Life (1000 hrs min.) LED Indicator lights when fuse is blown
- RoHS Compliant



NTE Type No.	Rated Current	Color Code	Diag No.
74-LAF3A	3A	Violet	F-13
74-LAF5A	5A	Tan	F-13
74-LAF7.5A	7.5A	Brown	F-13
74-LAF10A	10A	Red	F-13
74-LAF15A	15A	Blue	F-13
74-LAF20A	20A	Yellow	F-13
74-LAF25A	25A	Natural	F-13
74-LAF30A	30A	Green	F-13

F-13



Specifications

Rated Voltage: 32V

LED Voltage Rating: 12VDC, 24VDC, 32VDC

LED Lifetime: around 1000 hours at +60°C. The resin won't be melted under +130°C.

Time Current Characteristics:

% of Ampere Rating	Opening Time
110%	100 hours min.
135%	0.75 seconds min.
200%	0.15 seconds min.
350%	0.08 seconds min.

Accessories:

Description	NTE Type No.
In-Line Fuse Holder, up to 15A	74-IFHA15
In-Line Fuse Holder, up to 30A	74-IFHA30
In-Line Fuse Holder w/LED Light, up to 15A	74-IFHAL15
In-Line Fuse Holder w/LED Light, up to 30A	74-IFHAL30