


RoHS 2.0

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A1.	/.	新版发行	2022. 12. 02	LZR
A2.	/.	新增标注	2024. 03. 28	LZR



3D

PIN	DIM A	DIM B	DIM C
2P	10.00	6.10	2.50
3P	12.50	8.60	5.00
4P	15.00	11.10	7.50
5P	17.50	13.60	10.00
6P	20.00	16.10	12.50

SPECIFICATION

- 1.Contact resistance:  $\leq 10M\Omega$
- 2.Insulation resistance:  $\geq 1000M\Omega$
- 3.Rated voltage: 250 V AC DC
- 4.Rated current: 3.0 A AC DC
- 5.Withstand Voltage: 1000V AC/minute
- 6.Temperature Range :  $-25^{\circ}C \sim +85^{\circ}C$

C	插片	黄铜+65	镀镍锡	
B	插针	黄铜+65	镀镍锡	
A	底座	LCP	本色	
序号	品名	材质	电镀/颜色	备注

深圳市虹成电子有限公司

UNLESS OTHERWISE, GENERAL TOLERANCE:		NAME: 2.54针座2PIN卧贴		P/N: HCZZ0021-2	
X. xxx $\pm 0.10$				DWG NO:	
X. xx $\pm 0.20$					
X. x $\pm 0.30$					
ANGULAR:		THIRD ANGLE PROJECTION		UNIT: MM	
X. xx° $\pm 1^{\circ}$				SCALE: 1:1	
X. x° $\pm 3^{\circ}$				SIZE: A4	
X. ° $\pm 5^{\circ}$				SHEET: 1/1	
		DRAWN:		REV: A1	
		CHECKED:		APPROVED:	

RECOMMENDER P.C.B.LAYOUT TOP VIEW  
(COMPONENT SIDE TOLERANCE  $\pm 0.1$ )

