





RoHS 2.0

| REV. | ECN NO. | DESCRIPTION | DATE | DESIGN |
|------|---------|-------------|--------------|--------|
| A1. | /. | 新版发行 | 2022. 12. 02 | LZR |
| A2. | /. | 新增标注 | 2024. 03. 28 | LZR |





| PIN | DIM A | DIM B | DIM C |
|-----|-------|-------|-------|
| 2P | 10.00 | 6.10 | 2.50 |
| 3P | 12.50 | 8.60 | 5.00 |
| 4P | 15.00 | 11.10 | 7.50 |
| 5P | 17.50 | 13.60 | 10.00 |
| 6P | 20.00 | 16.10 | 12.50 |



SPECIFICATION

- Contact resistance: $\leq 10M\Omega$
- Insulation resistance: $\geq 1000M\Omega$
- Rated voltage: 250 V AC DC
- Rated current: 3.0 A AC DC
- Withstand Voltage: 1000V AC/minute
- Temperature Range : $-25^{\circ}C \sim +85^{\circ}C$



| | | | | |
|----|----|-------|-------|----|
| C | 插片 | 黄铜+65 | 镀镍锡 | |
| B | 插针 | 黄铜+65 | 镀镍锡 | |
| A | 基座 | LCP | 本色 | |
| 序号 | 品名 | 材质 | 电镀/颜色 | 备注 |

深圳市虹成电子有限公司

| | | | | |
|--|----------------------------|--|-----------------|---------------|
| UNLESS OTHERWISE, GENERAL TOLERANCE: X. xxx ±0.10 X. xx ±0.20 X. x ±0.30 | NAME: 2.54针座4PIN卧贴 | | P/N: HCZZ0021-4 | |
| | THIRD ANGLE PROJECTION | | UNIT: MM | SCALE: 1:1 |
| ANGULAR: X. xx° ±1° X. x° ±3° X. ° ±5° | DRAWN: | | CHECKED: | APPROVED: |

RECOMMENDER P.C.B.LAYOUT TOP VIEW
(COMPONENT SIDE TOLERANCE±0.1)