


RoHS 2.0

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A1.	/.	新版发行	2022. 12. 02	LZR
A2.	/.	新增标注	2024. 03. 28	LZR

PIN	DIM A	DIM B	DIM C
2P	10.00	6.10	2.50
3P	12.50	8.60	5.00
4P	15.00	11.10	7.50
5P	17.50	13.60	10.00
6P	20.00	16.10	12.50



SPECIFICATION

- Contact resistance: $\leq 10\text{M}\Omega$
- Insulation resistance: $\geq 1000\text{M}\Omega$
- Rated voltage: 250 V AC DC
- Rated current: 3.0 A AC DC
- Withstand Voltage: 1000V AC/minute
- Temperature Range : $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$

序号	品名	材质	电镀/颜色	备注
C	插片	黄铜+65	镀镍锡	
B	插针	黄铜+65	镀镍锡	
A	基座	LCP	本色	

深圳市虹成电子有限公司

UNLESS OTHERWISE, GENERAL TOLERANCE:

X. xxx ±0.10
X. xx ±0.20
X. x ±0.30

ANGULAR:
X. xx° ±1°
X. x° ±3°
X. ° ±5°

NAME: 2.54针座5PIN卧贴 P/N: HCZZ0021-5
DWG NO:

THIRD ANGLE PROJECTION

UNIT:	SCALE:	SIZE:	SHEET:	REV.
MM	1:1	A4	1/1	A1

DRAWN: CHECKED: APPROVED:

RECOMMENDER P.C.B.LAYOUT TOP VIEW
(COMPONENT SIDE TOLERANCE±0.1)