




APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/19/09	
A		REVISED DIM.	6/13/11	
B		UPDATE SHAPE	9/23/14	AY
C		UPDATE SHAPE	2/22/17	AY/OC
D		UPDATE DIM.	9/5/18	AY/TY



SPECIFICATIONS:

Material:

- A. Cover: EVA+PE(2L), color Black
- B. Shell: ABS
- C. Metal Shield: Brass, Nickel plated
- D. Housing: Nylon6+FB
- E. Contact: Brass, Silver plated

Electrical:

Rating: 100V AC 1A Max
 Insulation resistance: 50 Mohms min. @500V DC
 Dielectric withstanding voltage: 500V AC for 1 minute

Mechanical:

Suggested Wire Gauge: 26-30 awg

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED			
INCHES		HOLES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

ADAM TECH
INTERCONNECTS
 909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

APPROVALS		DATE
DRAWN	DY	11/19/09
CHECKED		
APPROVED		

TITLE MINI DIN PLUG, ASSEMBLY TYPE			
SIZE X	PART NO. MDP-00X	REV. D	
REF: S00067T	SCALE: NTS	SHEET 1 OF 1	