


PCB.WELDING DRAWING (TOLERANCE:±0.05)

Main technical performance	
Rated electrical load	DC 24V 3A
Contact resistance	≤30mΩ
Insulation resistance	≥100MΩ
Pressure resistance	AC 500V 1min
Insertion force	3-30N
Operating temperature range	-20C°~+70C°
service life	5000cycles



SCHEMATIC

6	弹片	1	H65	镀银
5	插片	1	H62	镀银
4	平片	1	H62	镀银
3	中心针	1	H62	铜锡
2	盖板	1	PPA	黑
1	底座	1	PPA	黑
序号	名称	数量	材料	备注

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: DC SOCKET	
DECIMALS:			PAR DC-012A-B250
ANGLES:			DWN
X.X±0.30	X.*±5°		CHKD
X.XX±0.25	X.X*±1°		APVD
X.XXX±0.15		CUSTOMER COPY	SCALE N:A UNIT:MM
			SIZE:A4 SHEET:1F1
			REV:A