

**Description**: PIN 25x25x7 GPS Active Antenna

PART NUMBER: ANT2525JB08B1575A

## Features:

- Size: 25.0x25.0x7.0 mm
- High radiation efficiency
- Integrated LNA
- · Flexible cable/connector option
- RoHS compliant

# **Applications:**

- · Navigation device
- Telematics box
- Tracker

### Ceramic Patch Antenna ELECTRICAL SPECIFICATIONS

Description
Dimension
Centre Frequency
Gain
VSWR
Polarization
Impedance
Axis Ratio

**Beam Width** 

VALUE 25×25×4 mm³ GPS 1575 ± 2 MHz 5.5 dBic (Typ.) 2.0 Max.

Right Hand Circular Polarization 50Ω

 $\leq$  3dB

> 150 Degrees

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION

RoHS

This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and rederal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden. For more information:



**Description**: PIN 25x25x7 GPS Active Antenna

PART NUMBER: ANT2525JB08B1575A

## LNA ELECTRICAL SPECIFICATIONS

Description	VALUE
Centre Frequency	1575 ± 1.023 MHz
Gain	16 dB(Typ.)
Output VSWR	1.5 (Max.)
Noise Figure	1.4 dB (Typ.)
Supply Voltage	$3.0 \pm 0.3 V$
Current Consumption	5.0 mA (Typ.)
Power Consumption	15.0 mW (Typ.)
Output Impedance	50Ω
Operating Temperature	-30 ~ +85 °C
Humidity	< 95% .
Storage Temperature	-40 ~ +125 ℃

#### **NOTE**


- 1. Based on 70×70 mm<sup>2</sup> ground plane (with customer's housing)
- 2. Centre frequency will be offset to working frequency while changes of customer's housing and ground plane.
- 3. Please contact local sales if you need customized design to gain optimum antenna performance.



**Description**: PIN 25x25x7 GPS Active Antenna

PART NUMBER: ANT2525JB08B1575A

## **ELECTRICAL SPECIFICATIONS**



Length	25.0 +/- 0.2 mm
Width	25.0 +/- 0.2 mm
Thickness	6.9 +/- 0.2 mm
Cable	Diameter= 1.13 mm; Length= 75 mm
Connector	l-pex
Shielding Case	15×14×2 mm



**Description**: PIN 25x25x7 GPS Active Antenna

PART NUMBER: ANT2525JB08B1575A

REVISION HISTORY					
Revision	Date	Description			
Version 1	Nov. 23, 2020	- New issue	_		