


4 3 2 1

D

D





- NOTES:
- 1.RATING: 5A125/250VAC.
  - 2.OPERATING FORCE: 10~50gf
  - 3.CONTACT RESISTANCE: <50mΩ
  - 4.INSULATION RESISTANCE: >100MΩ(500VDC BETWEEN OPEN CONTACTS)
  - 5.DIELECTRIC STRENGTH: >1500Vac 0.5mA 1 MINUTE
  - 6.COLOR: BLACK

TEL: 0769-82310510-867

C

C



B

B

A

A

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4	→	9	→	RANGE	TOLERANCE			LMC	LMC	SCALE	FIT		
3	→	8	→	X	±0.5					MAT'L	***	DRAWING NO.	
2	→	7	→	X.X	±0.3					MATERIAL NO.			REV.
1	→	6	→	X.XX	±0.2			2016.11.23	2016.11.23				
NO	DESCRIPTION	NO	DESCRIPTION	ANGLE	±1°	ROCK TEK ELECTRICAL(SHENZHEN) CO.,LTD.				RTM2-6C4S05A050	*****	A	

4 3 2 1