


CIRCUIT DIAGRAM:



TEL: 0769-82310511-867

NOTES :

- 1.Circuit : ON/OFF
- 2.Operation force : 800±300gf
- 3.Rating : 16A 125/250VAC 3/4HP 125/250VAC(CUL)
16(4)A 125/250V~ T125/55 5E4 (ENEC17;NEMKO;CB)
16(4)A 250~ T125/55 1E4 (CQC)
- 4.Contact resistance : <30mΩ
5. Insulation resistance : >100MΩ(500VDC between open contacts)
- 6.Dielectric strength : >1500Vac 0.5mA 1 minute
- 7.Actuator color : WHITE
Housing color : BLACK

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM	
4	→	9	→	RANGE	TOLERANCE				LMC	SCALE	NO	
3	→	8	→	X	±0.3				2017. 05. 24	MAT'L	***	
2	→	7	→	X.X	±0.2					MATERIAL NO.	DRAWING NO.	REV.
1	→	6	→	X.XX	±0.1					MPS21-WBBDD-R D/C	WIF117005	A0
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1'	ROCK TEK ELECTRONIC(SHENZHEN) CO.,LTD.						

4

3

2

1