



scetion A-A

TEL: 0769-82310511-867

- NOTES:
- 1.Rating : 2.5A 250VAC CCC VDE  
5A 250VAC UL CUL
  - 2.Contact resistance : 50mΩ Max
  - 3.Insulation resistance : >100MΩ (Min) 500VDC
  - 4.Dielectric strength : >2000VAC 0.5mA 1 minutes

1	BODY	PC UL94V-2	Black	1
2	1# terminal	C2680 1/2H	Tin-plating	2
1	1# PIN	C3602	Ni-plating	2
NO.	PART NAME	MATERIAL		Q'TY

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4	→	9	→	RANGE	TOLERANCE				LMC	SCALE	NO		
3	→	8	→	X	±0.30				2019.05.20	MAT'L	***		
2	→	7	→	X.X	±0.20					MATERIAL NO.		DRAWING NO.	REV.
1	修改UL刻字 2021.05.22	6	→	X.XX	±0.10					RT-C08-C2-BA		WIF120083	A1
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1'	LEGIION ELECTRONIC & HARDWARE CO., LTD.							

4 3 2 1