Ы



KSC11 Series Sealed Tact Switch for SMT

Features/Benefits



- Hard actuator
- Long life
- Positive tactile feeling
- IP67 sealed
- SMT

Typical Applications

- Gaming/ Drones
- Industrial
- Medical
- High-end consumer
- Avionics

Specification

FUNCTION: Normally open CONTACT TYPE: SPST NO TERMINALS: J bend for SMT CONTACT MATERIAL: Silver plated

Environmental

OPERATING TEMPERATURE: -40°C to 85°C

Mechanical

Туре	Force (N)	Life	Travel (mm)
KSC1101J LFS	1.60 ±0.4	3,000,000	0.20 ±0.1
KSC1131J LFS	3.20 ±0.6	2,000,000	0.25 ±0.15
KSC1151J LFS	5.00 ±1.0	1,000,000	0.40 ±0.15

Electrical

MAXIMUM POWER: 1 VA

MIN. / MAX. VOLTAGE: 0.02V / 32V MIN. / MAX. CURRENT: 1 mA / 50 mA DIELECTRIC STRENGTH: 250 Vrms CONTACT RESISTANCE: ≤ 100 mΩ INSULATION RESISTANCE: (100V): 1000 MΩ

BOUNCE TIME: ≤ 5 ms

Soldering

This component is suited to the following methods:

- Cleaning according to typical washing processes

- Lead free reflow soldering process in accordance with IEC 61760-1


Packaging

In reels of 1,700 pieces Width of carrier tape: 16 mm Dimensions of reels: 380 mm

How To Order

Our easy build-a-switch concept allows you to mix and match options to create the switch you need. To order, select desired option from each category and place it in the appropriate box.


For any part number different from those listed above, please consult your local representative.






















First Angle Projection

