


SCH114

SMD POWER INDUCTORS





• Features

1. Open frame construction
2. Excellent Power Density
3. Engineered to Provide High Efficiency

CHARACTERISTICS



Part Number	Inductance (uH) (1)	Test Frequency	DC Resistance (Ω MAX) (2)	Saturation Current (A) (3)	Temperature Current (A) (4)
SCH114-2R5	2.5	100KHZ	30m	6.50	5.10
SCH114-3R9	3.9	100KHZ	37m	5.50	4.70
SCH114-4R7	4.7	100KHZ	44m	5.10	4.50
SCH114-5R6	5.6	100KHZ	48m	4.80	4.10
SCH114-6R8	6.8	100KHZ	54m	4.50	3.70
SCH114-8R6	8.6	100KHZ	60m	4.20	3.40
SCH114-100	10	100KHZ	66m	4.00	3.10
SCH114-120	12	100KHZ	68m	3.80	2.90
SCH114-150	15	100KHZ	74m	3.50	2.75
SCH114-180	18	100KHZ	85m	3.40	2.55
SCH114-220	22	100KHZ	100m	3.00	2.37
SCH114-270	27	100KHZ	114m	2.70	2.18
SCH114-330	33	100KHZ	122m	2.50	2.05
SCH114-390	39	100KHZ	139m	2.30	1.95
SCH114-470	47	100KHZ	175m	2.00	1.80
SCH114-560	56	100KHZ	194m	1.90	1.70
SCH114-680	68	100KHZ	241m	1.70	1.58
SCH114-820	82	100KHZ	289m	1.45	1.40
SCH114-101	100	100KHZ	352m	1.32	1.20
SCH114-121	120	100KHZ	397m	1.23	1.08
SCH114-151	150	100KHZ	492m	1.10	0.96
SCH114-181	180	100KHZ	589m	1.00	0.90
SCH114-221	220	100KHZ	747m	0.90	0.80
SCH114-271	270	100KHZ	927m	0.72	0.68
SCH114-331	330	100KHZ	1.22	0.70	0.56
SCH114-391	390	100KHZ	1.30	0.62	0.52
SCH114-471	470	100KHZ	1.56	0.60	0.50



- (1). Inductance tolerance for 2.5uH~8.6uH: $\pm 30\%$, for 10uH~56uH: $\pm 20\%$, for 68uH~470uH: $\pm 10\%$. Tested at 0.25V, 0ADC and 25°C
- (2). DCR easured at 25°C.
- (3). The DC current at which the inductance decreases by 10% from its initial value.
- (4). The DC current that results in a 40°C temperature rise from 25°C ambient.

[Click here for QUANTITY PER REEL & PACKING INFORMATION](#)

Custom versions available upon request.

© 2019 Signal Transformer –Specification subject to change without notice. 12.19



belfuse.com/signal

128 Atlantic Avenue, Lynbrook, NY 11563
Toll Free 866-239-5777 • Tel 516-239-5777 • Fax 516-239-7208
Sales@signaltransformer.com • techhelp@signaltransformer.com