



### Performance parameters

Product name	WIFI Antenna
Model Type	KH-4G-SMA-108
Frequency Range	800-2700MHZ
Vswr	≤2.0
Gain	2DBi
Impedance	50 Ω
Polarization	Vertical
Radiation	<b>OMNIDIRECTIONAL</b>
Max power	10 W
Connector	SMAJ
Dimensions	108mm*10mm
Shell material	ABS
Installation	screw
Temperature	-35° -- 75°
Weight	10 ± 3g

DWN BY/DATE JIANG 16-10-29	DESG BY/DATE	TOLERANCES .X± .XX± .XXX± ANGLES±	SCALE 1 : 1		ENG PROJECT NO. YG1610291102	深圳金航标电子有限公司	WWW.BDS666.COM
CHK BY/DATE	APPD BY/DATE		UNIT m / m	SH 1 OF 1	CONTROL NO. YG-HD06	型号: KH-4G-SMA-108	0755-83044319