


Kinghelm®

REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN			



1代端子

L=80~200MM

NOTES:

1. ELECTRICAL:
 - 1.1. VOLTAGE RATING:DCV 300V 10MS
 - 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
 - 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
 - 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
 - 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
2. MATERIAL:
 - 2.1. SEE TABLE
3. ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
④	套管	黑色热缩套管, OD:2.0MM	AS
③	端子	高仿I-PEX 1.13 1代端子, 镀金	1
②	接头	SMA母头母针, 一体4脚半牙, 镀金, 外螺纹内孔	1
①	同轴线	RF1.13cable, 黑色同轴线, OD:1.10mm	AS

深圳市金航标电子有限公司

www.kinghelm.com.cn

KH-IPEX-SMAKWE-B80H

0755-28190160

ALL DIMENSION
ARE IN MM

DRAWN Jamy DATE 2022-12-12

ENG.

COMPUTER GENERATED
IN SOLIDWORKS


MFG.

DO NOT SCALE
THIS DRAWING

Q.A.

I-PEX 1.13 TO SMA母头4脚半牙
不带凹槽 L=80mm

PROJECTION



GENERAL TOLERANCE FOR
ANGLES X.X X.XX X.XXX
± 1° ± 0.3 ± 0.25 ± 0.150

SIZE Number

B

REV

A

SCALE: Free

TYPE

SHEET 1 OF 1

CUSTOMER P/N: