


代码: KHB65-37(11)-28-A/3

REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN			



出貨時另外附配件出貨(防水圈, 华司, 螺母, 垫片, 红帽子)

NOTES:

1. ELECTRICAL:
  - 1.1. VOLTAGE RATING:DCV 300V 10MS
  - 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
  - 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
  - 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
  - 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
2. MATERIAL:
  - 2.1. SEE TABLE
3. ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
④	套管	黑色热缩套管, OD:2.0MM	AS
③	端子	高仿I-PEX ,1.13端子, 镀金	1
②	接头	SMA防水母头母针, 后塞, 11牙, 镀金	1
①	同轴线	RF 1.13灰色线,OD:1.13mm	AS

**Kinghelm®** 深圳市金航标电子有限公司

ALL DIMENSION ARE IN MM	DRAWN Jamy	DATE 2022-06-06	I-PEX 1.13 TO SMA 11牙防水母头 L=65mm
	ENG.		
COMPUTER GENERATED IN SOLIDWORKS	MFG.		
DO NOT SCALE THIS DRAWING	Q.A.		
PROJECTION	GENERAL TOLERANCE FOR ANGLES		SIZE Number
	X.X X.XX		REV A
	± 1' ± 0.3 0.25 0.150		SCALE: Free TYPE
CUSTOMER P/N:			SHEET 1 OF 1