



## Main

Range of Product	Telemecanique Inductive proximity sensors XS
Series name	General purpose
Sensor Type	Inductive proximity sensor
Product Specific Application	-
Sensor name	XSD
Sensor design	Form 80 x 80 x 40
Size	40 mm
Body type	Fixed
Enclosure Material	Plastic
Type of output signal	Discrete
Wiring Technique	2-wire
[Sn] nominal sensing distance	1.57 in (40 mm)
Discrete output function	1 NO or 1 NC programmable
Electrical connection	Screw-clamp terminals
[Us] rated supply voltage	12...240 V AC
IP degree of protection	IP67

## Complementary

Detection face	5 positions turret head
Detector flush mounting acceptance	Non flush mountable
Material	Plastic
Front material	Plastic
Output circuit type	AC
Cable entry	1 entry tapped for Pg 13.5 cable gland
Switching frequency	<= 10 Hz
Depth	1.57 in (40 mm)
Height	3.94 in (100 mm)
Width	3.15 in (80 mm)
Net Weight	1.06 lb(US) (0.48 kg)

## Environment

Product Certifications	CCC
Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)

## Ordering and shipping details

Category	22486-SENSORS, PROXIMITY
Discount Schedule	DS2
GTIN	3389110619942
Nbr. of units in pkg.	1
Package weight(Lbs)	17.64 oz (500.0 g)
Returnability	No
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.05 in (5.2 cm)
Package 1 width	5.83 in (14.8 cm)
Package 1 Length	3.46 in (8.8 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	11
Package 2 Weight	12.63 lb(US) (5.727 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------