



General Specification
 Current Rating: 1.5A DC /Contact, 20mA DC for LED signals
 Voltage Rating: 125V AC /Contact, 2.0 volts DC for LED signals
 Operating Environment
 Standard Temperature: -20°C~+70°C
 Industrial Temperature: -40°C~+85°C
 Humidity: 20~70%
 Contact Resistance: ≤30mΩ
 Insulation Resistance: ≥500MΩ
 Dielectric Strength: 500V AC/(50HZ)/Min
 Mating And Unmating Force: 3~20N
 Durability: 750 Cycles Min

Material Specification
 Housing: Thermo-plastic, UL94V-0.
 Contact: Alloy Copper
 Shield: Alloy Copper

Please refer to the customer drawing when customer has specified

网络插座外形图

绘图: 樊飞 日期: 2022.4.6

审核: 陈伟 日期:

核准: 李华 日期:

序号	名称	材料	数量	键层/颜色	备注
4	LED灯	树脂/PE	2	NI/AG	
3	后盖	PA66	1	BLACK	
2	插针	PHOSPHOR BRONZE	8	"P1"	
1	塑座	PA46	1	BLACK	



温州瑞川电子有限公司
 WEN ZHOU RUI CHUAN ELECTRONIC CO., LTD.

品名: RCH-52-42(全塑带灯)黄绿 正负

料号: 5242-8Y(G00010A)B32 (RC01005)

型号: RJ45 图号: 20210904-09

公差: ±0.25
 料号: ±0.30
 角度: ±0.15
 版本: 1 of 1
 单位: mm
 比例: 1:1
 纸张: A4

1	2	3	变更单号	该图面供温州瑞川电子有限公司内部使用,不得私自复印
版本	变更履历	日期	绘制日期	
A/0	新出版发行			