



General Specification
 Current Rating: 1.5A DC /Contact, 20mA DC for LED signals
 Voltage Rating: 125V AC /Contact, 2.0 volts DC for LED signals
 Operating Environment
 Standard Temperature: -20°C~+70°C
 Industrial Temperature: -40°C~+85°C
 Humidity: 20~70%
 Contact Resistance: ≤30mΩ
 Insulation Resistance: ≥500MΩ
 Dielectric Strength: 500V AC/(50HZ)/Min
 Mating And Umating Force: 3~20N
 Durability: 750 Cycles Min

Material Specification
 Housing :Thermo-plastic, UL94V-0.
 Contact :Alloy Copper
 Shield :Alloy Copper

Please refer to the customer drawing when customer has specified

网络插座外形图

3	外壳	H62	1	NI	
2	插针	PHOSPHOR BRONZE	8	FU*	
1	塑座	LCP	1	BLACK	
序号	名称	材料	数量	镀层/颜色	备注



温州瑞川电子有限公司
 WEN ZHOU RUI CHUAN ELECTRONIC CO., LTD.

日期:	日期:	日期:	日期:
审核:	审核:	日期:	日期:
日期:	日期:	日期:	日期:

一般公差	品名:	RJ45	
±0.20	料号:	8102-80002010LB22 (RC021117-B)	
±0.30	型号:	RJ45	
±0.15	图号:		
角度: ±2°	版本:	A/0	
页面: 1 of 1	单位:mm	比例: 1:1	纸张: A4